

HERMA 100

Fast and easy hand labelling

By using the **HERMA 100** even hand labelling can become an efficient, fast and easy operation. The **HERMA 100** is an electrically driven unit that automatically dispenses labels on demand. The waste backing paper is rewound for safety and ease of disposal. Reliability, ease of use and a small footprint are the main features of the **HERMA 100**.

The **HERMA** dispenser is available for reel widths of up to 80 mm or 160 mm.

Advantages of the **HERMA 100** dispensers:

- > HERMA dispensers are high-quality products with a one-year warranty. The **HERMA 100** dispensers are CE compliant.
- > If your dispenser should break down we will repair it within 24 hours or furnish a free replacement during the warranty period.
- > HERMA offers the quality and dependability of an internationally known manufacturer of labelling machines. These advantages are also yours when buying a manual label dispenser.



HERMA 100



HERMA 100 dispenser for reel widths of up to 160 mm

Technical specifications HERMA 100 dispenser

Reel width	max. 80 mm or 160 mm
Diameter label reel	max. 130 mm
Diameter reel core	any
Label winding	inside
Power supply	100-240V~ / 50-60 Hz
Power consumption	40 W
Class of protection	IP20 <input type="checkbox"/>
Dimensions HERMA 100/8 (LxWxH, approx.)	216x116x160 mm
Dimensions HERMA 100/16 (LxWxH, approx.)	216x196x160 mm

We are constantly endeavouring to improve our products.
All technical data is therefore subject to change without prior notice.

Self-adhesive labels

Are practical, useful and particularly convenient. Whether for decoration or conveying important information – they are applied efficiently and accurately with the **HERMA 100** label dispenser.

HERMA dispensers are easy to use, extremely robust and very economical.

HERMA GmbH
Labelling Systems Division
73779 Deizisau / Germany
www.herma.com
www.herma-labeler.com

Reel holder for large rolls

This enables the **HERMA 100** to use labels reels with diameters of up to 250 mm. The manual dispenser is simply placed upon the base plate of the reel holder and fixed by means of pins.

